


D0-10ND3F Cut Sheet



DirectLOGIC DL05/06 discrete input module, 10-point, 12-24 VDC, sinking/sourcing, fast response, 2 isolated common(s), 5 point(s) per common. Removable terminal block included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/D0-10ND3F>

Technical Specifications

| | |
|----------------------------------|-----------------------------------------------|
| Brand | DirectLOGIC |
| Item | Input module |
| I/O Module Type | Discrete |
| Series | DL05/06 |
| Number of Input Points | 10 |
| Nominal Input Voltage | 12-24 VDC |
| Discrete Input Type | Sinking/sourcing |
| Fast Response | Yes |
| Number of Isolated Input Commons | 2 |
| Number of Points per Common | 5 |
| Includes | Removable terminal block |
| Programming Software | DirectSOFT programming software v4.0 or later |

Agency Approvals

| | |
|----------------------|----------------------------------------|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |