


D0-10TD1 Cut Sheet



DirectLOGIC DL05/06 discrete output module, 10-point, 6-24 VDC, sinking, 2 common(s), 5 point(s) per common, 0.3A/point, 1.5A/common. Removable terminal block included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/D0-10TD1>

Technical Specifications

Brand	DirectLOGIC
Item	Output module
I/O Module Type	Discrete
Series	DL05/06
Number of Output Points	10
Nominal Output Voltage	6-24 VDC
Discrete Output Type	Sinking
Number of Non-Isolated Output Commons	2
Number of Points per Common	5
Load Current	0.3A/point, 1.5A/common
Fuse Type	User-supplied external fuse
Includes	Removable terminal block
Programming Software	DirectSOFT programming software v4.0 or later

Agency Approvals

UL Listed File #	E157382
UL Recognized File #	None
UL Hazardous File #	E200031
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document