

# D2-08CDR Cut Sheet



DirectLOGIC DL205 discrete combo module, Input: 4-point, 24 VDC, sinking/sourcing, Output: 4-point, 6-24 VDC/6-240 VAC, (1) Form A (SPST) relay, 1A/point, 4A/module.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/D2-08CDR>

## Technical Specifications

<b>Brand</b>	DirectLOGIC
<b>Item</b>	Combo module
<b>I/O Module Type</b>	Discrete
<b>Series</b>	DL205
<b>Number of Input Points</b>	4
<b>Nominal Input Voltage</b>	24 VDC
<b>Discrete Input Type</b>	Sinking/sourcing
<b>Number of Non-Isolated Discrete Input Commons</b>	1

<b>Number of Output Points</b>	4
<b>Nominal Output Voltage</b>	6-24 VDC/6-240 VAC
<b>Relay Configuration</b>	(1) Form A (SPST) relay
<b>Number of Non-Isolated Discrete Output Commons</b>	1
<b>Load Current</b>	1A/point, 4A/module
<b>Fuse Type</b>	Replaceable fuse
<b>Programming Software</b>	DirectSOFT programming software v4.0 or later

## Agency Approvals

<b>UL Listed File #</b>	E157382
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	see CSA
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	234884
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/D2-08CDR.pdf>  
See store item page for other formats.