


# D2-12TR Cut Sheet



DirectLOGIC DL205 relay output module, 12-point, 6-24 VDC/6-240 VAC, (12) Form A, 2 common(s), 6 point(s) per common, 1.5A/point max, 3A/common. Removable terminal block included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/D2-12TR>

## Technical Specifications

Brand	DirectLOGIC
Item	Output module
I/O Module Type	Relay
Series	DL205
Number of Output Points	12
Nominal Output Voltage	6-24 VDC/6-240 VAC
Relay Configuration	(12) Form A (SPST) relays
Number Of Commons	2
Jumper Selectable Isolation	No
Number of Points per Common	6
Load Current	1.5A/point max, 3A/common
Fuse Type	Replaceable fuse
Includes	Removable terminal block
Programming Software	DirectSOFT programming software v4.0 or later

## Agency Approvals

UL Listed File #	E157382
UL Recognized File #	None
UL Hazardous File #	see CSA
CE	<a href="#">View CE declarations</a>
CSA File #	234884
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>