

D2-262 Cut Sheet



DirectLOGIC DL205 CPU, 15.8k words ladder memory, (1) RS-232 (RJ12) and (1) RS-232/RS-422/RS-485 (DB15HD female) port(s). Purchase D2-BAT-1 backup battery separately.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/D2-262>

Technical Specifications

Brand	DirectLOGIC
Item	CPU
Series	DL205
Total Memory	30.4k words
Ladder Memory	15.8k words
User Data Memory	14.6k words
Programming Language	Ladder
Programming Software	DirectSOFT programming software v6.3 or later
Communication Port and Connection Type(s)	<ul style="list-style-type: none">• (1) RS-232 (RJ12)• (1) RS-232/RS-422/RS-485 (DB15HD female)
Port Protocol(s)	<ul style="list-style-type: none">• DirectNET• Modbus RTU• ASCII• K-sequence• serial remote I/O• programming and monitoring

Port Speed(s)	<ul style="list-style-type: none">• fixed at 9.6k baud• up to 38.4k baud
Real Time Clock/Calendar	Yes
Retentive Memory	Yes
Battery Backup	Yes
Maximum Number of PID Loops	16
Additional Information	Purchase D2-BAT-1 backup battery separately

Agency Approvals

UL Listed File #	E157382
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document