


D2-32TD2 Cut Sheet



DirectLOGIC DL205 discrete output module, 32-point, 12-24 VDC, sourcing, 4 isolated common(s), 8 point(s) per common, 0.1A/point, 3.2A/module. Requires ZIPLink pre-wired cable.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/D2-32TD2>

Technical Specifications

Brand	DirectLOGIC
Item	Output module
I/O Module Type	Discrete
Series	DL205
Number of Output Points	32
Nominal Output Voltage	12-24 VDC
Discrete Output Type	Sourcing
Number of Isolated Output Commons	4
Number of Points per Common	8
Load Current	0.1A/point, 3.2A/module
Fuse Type	User-supplied external fuse
Requires	ZIPLink pre-wired cable
Programming Software	DirectSOFT programming software v4.0 or later

Agency Approvals

UL Recognized File #	None
UL Hazardous File #	E200031
CE	View CE declarations
CSA File #	234884
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document