

D232320DT-M Cut Sheet



NITRA pneumatic cylinder, NFPA tie rod, 2in bore, 5/8in rod diameter, 32in stroke, double acting, magnetic piston, tapped end caps mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/D232320DT-M>

Technical Specifications

| | |
|----------------------|------------------|
| Brand | NITRA |
| Item | Cylinder |
| Working Fluid | Air or inert gas |
| Cylinder Type | NFPA tie rod |
| Bore Diameter | 2in |
| Stroke | 32in |
| Port Size | 1/4in female NPT |
| Mounting | Tapped end caps |

| | |
|-------------------------|---------------------|
| Action Type | Double acting |
| Magnetic Piston | Magnetic piston |
| Body Material | Aluminum |
| End Cap Material | Aluminum |
| Rod Material | Chrome-plated steel |
| Rod Diameter | 5/8in |
| Rod Thread Size | 7/16-20 |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/D232320DT-M.pdf>
See store item page for other formats.