

D4-08ND3S Cut Sheet



DL405 discrete input module, 8-point, 24-48 VDC, sinking/sourcing, 8 isolated common(s), 1 point(s) per common. Removable terminal block included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/D4-08ND3S>

Technical Specifications

Brand	DL405
Item	Input module
I/O Module Type	Discrete
Number of Input Points	8
Nominal Input Voltage	24-48 VDC
Discrete Input Type	Sinking/sourcing
Number of Isolated Input Commons	8
Number of Points per Common	1
Includes	Removable terminal block
Programming Software	DirectSOFT programming software v4.0 or later

Agency Approvals

UL Listed File #	E157382
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/D4-08ND3S.pdf>
See store item page for other formats.