

D4-08TR Cut Sheet



DirectLOGIC DL405 relay output module, 8-point, 6-24 VDC/6-240 VAC, (8) Form A, 2 isolated common(s), 4 point(s) per common, 2A/point, 5A/common. Removable terminal block included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/D4-08TR>

Technical Specifications

Brand	DirectLOGIC
Item	Output module
I/O Module Type	Relay
Series	DL405
Number of Output Points	8
Nominal Output Voltage	6-24 VDC/6-240 VAC
Relay Configuration	(8) Form A (SPST) relays
Number of Isolated Commons	2

Jumper Selectable Isolation	No
Number of Points per Common	4
Load Current	2A/point, 5A/common
Fuse Type	User-supplied external fuse
Includes	Removable terminal block
Programming Software	DirectSOFT programming software v4.0 or later

Agency Approvals

UL Listed File #	E157382
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/D4-08TR.pdf>
See store item page for other formats.