

D4-16ND2 Cut Sheet



DirectLOGIC DL405 discrete input module, 16-point, 12-24 VDC, sourcing, 2 isolated common(s), 8 point(s) per common. Removable terminal block included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/D4-16ND2>

Technical Specifications

Brand	DirectLOGIC
Item	Input module
I/O Module Type	Discrete
Series	DL405
Number of Input Points	16
Nominal Input Voltage	12-24 VDC
Discrete Input Type	Sourcing
Fast Response	No
Number of Isolated Input Commons	2
Number of Points per Common	8
Includes	Removable terminal block
Programming Software	DirectSOFT programming software v4.0 or later

Agency Approvals

UL Listed File #	E157382
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/D4-16ND2.pdf>
See store item page for other formats.