

D4-16NE3 Cut Sheet



DirectLOGIC DL405 discrete input module, 16-point, 12-24 VAC/VDC, sinking/sourcing, 2 isolated common(s), 8 point(s) per common. Removable terminal block included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/D4-16NE3>

Technical Specifications

| | |
|----------------------------------|---|
| Brand | DirectLOGIC |
| Item | Input module |
| I/O Module Type | Discrete |
| Series | DL405 |
| Number of Input Points | 16 |
| Nominal Input Voltage | 12-24 VAC/VDC |
| Discrete Input Type | Sinking/sourcing |
| Fast Response | No |
| Number of Isolated Input Commons | 2 |
| Number of Points per Common | 8 |
| Includes | Removable terminal block |
| Programming Software | DirectSOFT programming software v4.0 or later |

Agency Approvals

| | |
|----------------------|--|
| UL Listed File # | E157382 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/D4-16NE3.pdf>
See store item page for other formats.