

# D4-32TD2 Cut Sheet



DirectLOGIC DL405 discrete output module, 32-point, 12-24 VDC, sourcing, 4 isolated common(s), 8 point(s) per common, 0.2A/point, 1A/common, 4A/module. Requires ZIPLink pre-wired cable.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/D4-32TD2>

## Technical Specifications

Brand	DirectLOGIC
Item	Output module
I/O Module Type	Discrete
Series	DL405
Number of Output Points	32
Nominal Output Voltage	12-24 VDC
Discrete Output Type	Sourcing
Number of Isolated Output Commons	4
Number of Points per Common	8
Load Current	0.2A/point, 1A/common, 4A/module
Fuse Type	User-supplied external fuse
Requires	ZIPLink pre-wired cable
Programming Software	DirectSOFT programming software v4.0 or later

## Agency Approvals

UL Listed File #	E157382
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	<a href="#">View EU REACH document</a>