

DC-DAC25-10M Cut Sheet



SureMotion drive coupling hub, Oldham, aluminum alloy, clamp, size 25, 10mm bore. Requires DC-DDS25 torque disc.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DC-DAC25-10M>

Technical Specifications

Brand	SureMotion
Item	Drive coupling hub
Coupling Type	Oldham
Material	Aluminum alloy
Rated Torque	4 N-m
Maximum Angular Misalignment	3.0 degrees
Maximum Parallel Misalignment	0.41mm

Maximum RPM	3000
Attachment Style	Clamp
Coupling Size	25
Bore Diameter	10mm
Outside Diameter	25.4mm
Requires	DC-DDS25 torque disc

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/DC-DAC25-10M.pdf>
See store item page for other formats.