

# DC-DLSS40-08 Cut Sheet



SureMotion drive coupling, double loop, stainless steel, setscrew, size 40, 1/2in bore.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DC-DLSS40-08>

## Technical Specifications

|                                      |                 |
|--------------------------------------|-----------------|
| <b>Brand</b>                         | SureMotion      |
| <b>Item</b>                          | Drive coupling  |
| <b>Coupling Type</b>                 | Double loop     |
| <b>Material</b>                      | Stainless steel |
| <b>Rated Torque</b>                  | 10 N-m          |
| <b>Maximum Angular Misalignment</b>  | 15 degrees      |
| <b>Maximum Parallel Misalignment</b> | 3.2mm           |
| <b>Maximum RPM</b>                   | 3000            |
| <b>Attachment Style</b>              | Setscrew        |
| <b>Coupling Size</b>                 | 40              |
| <b>Bore Diameter</b>                 | 1/2in           |
| <b>Outside Diameter</b>              | 55.9mm          |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | None                                   |
| <b>UL Recognized File #</b> | None                                   |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | None                                   |
| <b>CSA File #</b>           | None                                   |
| <b>RoHS Status</b>          | No                                     |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |