


DC-JAC14-03 Cut Sheet



SureMotion drive coupling hub, jaw type, aluminum alloy, clamp, size 14, 3/16in bore. Requires DC-JS14 series spiders.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DC-JAC14-03>

Technical Specifications

| | |
|--------------------------------------|--------------------|
| Brand | SureMotion |
| Item | Drive coupling hub |
| Coupling Type | Jaw type |
| Material | Aluminum alloy |
| Maximum Angular Misalignment | 1.0 degrees |
| Maximum Parallel Misalignment | 0.05mm |

| | |
|-------------------------|------------------------|
| Maximum RPM | 27280 |
| Attachment Style | Clamp |
| Coupling Size | 14 |
| Overall Length | 21.8mm |
| Bore Diameter | 3/16in |
| Outside Diameter | 14mm |
| Requires | DC-JS14 series spiders |

Agency Approvals

| | |
|-----------------------------|----------------------------------------|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/DC-JAC14-03.pdf>
See store item page for other formats.