


# DN-24J2Y Cut Sheet



DINnector terminal block jumper, push-in type, 24-pole, orange, 25A, 600V rated (UL). Package of 5. For use with multiple terminal blocks.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DN-24J2Y>

## Technical Specifications

Brand	DINnector
Item	Terminal block jumper
Jumper Type	Push-in
Number of Poles	24
Color	Orange
Amperage Rating	25A
Voltage Rating	600V rated (UL)
Quantity per Pack	5
For Use With	Multiple terminal blocks

## Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/DN-24J2Y.pdf>  
See store item page for other formats.