


DN-D10LED1-A Cut Sheet



DINnector screw double-level feedthrough terminal block, connected between levels and power indicator, accepts wire size 24-10 AWG, gray, 30A, 12-24 VAC/VDC LED indicator(s), 35mm DIN rail mount, 100kA SCCR. Package of 10.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DN-D10LED1-A>

Technical Specifications

Brand	DINnector
Item	Terminal block
Connector Type	Screw
Terminal Block Type	Double-level feedthrough
Terminal Block Special Feature(s)	Connected between levels and power indicator
Wire Size	24-10 AWG
Color	Gray

Amperage Rating	30A
Voltage Rating	24 VDC
Indicator	12-24 VAC/VDC LED
Mounting	35mm DIN rail
SCCR Rating	100kA SCCR
Quantity per Pack	10
For Use With	Jumpers DN-24J4Y, DN-2J4Y and DN-3J4Y

Agency Approvals

UL Listed File #	None
UL Recognized File #	E179129
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/DN-D10LED1-A.pdf>
See store item page for other formats.