

# DPE32BL Cut Sheet



Schneider Electric Easy TeSys series IEC contactor, 32A, (3) N.O. power poles, (1) N.O. auxiliary contacts, 24 VDC coil voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DPE32BL>

## Technical Specifications

<b>Brand</b>	Schneider Electric
<b>Item</b>	Contactor
<b>Series</b>	Easy TeSys
<b>Contactor Type</b>	IEC
<b>Actuator Type</b>	Magnetic
<b>Amperage Rating</b>	32A
<b>Power Poles</b>	(3) N.O.
<b>Auxiliary Contacts</b>	(1) N.O.
<b>Coil Voltage</b>	24 VDC
<b>Horsepower Rating</b>	15hp
<b>SCCR Rating</b>	5kA SCCR
<b>UL Rating</b>	UL 60947-4-1
<b>Mounting</b>	35mm DIN rail or panel

## Agency Approvals

<b>UL Listed File #</b>	E164862
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	164581
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/DPE32BL.pdf>  
See store item page for other formats.