

DPM2L-AT-2R-HL Cut Sheet



ProSense digital panel meter, 1/8 DIN, 20mm 4-digit red LED, analog, RTD, thermocouple, potentiometer input, (2) 8A SPDT relays output, 20 to 265 VAC/11 to 265 VDC operating voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DPM2L-AT-2R-HL>

Technical Specifications

Brand	ProSense
Item	Digital panel meter
Mounting	Panel
Mounting Hole Size	1/8 DIN
Display Type	20mm 4-digit red LED
Input Current Signal Range	+/-20mA
Input Voltage Signal Range	+/-200VDC +/-10VDC
Input Thermocouple Signal Type	J, K, T, N
Input RTD Signal Types	Pt100 and Pt1000
Input Potentiometer Signal Range	100-100k Ohms
Output	(2) 8A SPDT relays
Operating Voltage	20 to 265 VAC/11 to 265 VDC
Loop Powered	No

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document