

DPM4-A-HS-L Cut Sheet



ProSense digital panel meter, panel mount, 1/8 DIN, 14 mm 5-digit red LED and 8 mm 1-digit green LED, analog, load cell or potentiometer input, 10–30 VDC operating voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DPM4-A-HS-L>

Technical Specifications

Brand	ProSense
Item	Digital panel meter
Mounting	Panel
Mounting Hole Size	1/8 DIN
Display Type	14 mm 5-digit red LED and 8 mm 1-digit green LED
Input	Analog, load cell or potentiometer
Input Current Signal Range	±20 mA

Input Voltage Signal Range	±1 VDC, ±5 VDC and ±10 VDC
Input Potentiometer Signal Range	200–100 k ohm
Input Load Cell Signal Range	±30 mVDC, ±60 mVDC, ±120 mVDC, ±300 mVDC and ±500 mVDC
Operating Voltage	10–30 VDC
Loop Powered	No

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/DPM4-A-HS-L.pdf>
See store item page for other formats.