

DR30B5-EBZC Cut Sheet



Fuji Electric audible alarm buzzer, 90 dB at 0.1m, 70 dB at 1m, 2.4 kHz to 3.3 kHz tone frequency, continuous/intermittent tone(s), 12 to 24 VAC/VDC, permanent LED indicator(s), red, 30mm, panel mount, plastic housing, silver, IP00.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DR30B5-EBZC>

Technical Specifications

Brand	Fuji Electric
Item	Audible alarm buzzer
Loudness Decibel	90 dB at 0.1m, 70 dB at 1m
Tone Frequency	2.4 kHz to 3.3 kHz
Tone Type	Continuous/intermittent
Touch to Acknowledge	No
Voltage Rating	12 to 24 VAC/VDC
Indicator	Permanent LED
Light Color(s)	Red
Barrel Size	30mm
Mounting	Panel
Housing Material	Plastic
Color	Silver
IP Rating	IP00

Agency Approvals

UL Listed File #	E44592
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	LR20479
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/DR30B5-EBZC.pdf>
See store item page for other formats.