

# DR30B5-HBZC Cut Sheet



Fuji Electric audible alarm buzzer, 90 dB at 0.1m, 70 dB at 1m, 2.4 kHz to 3.3 kHz tone frequency, continuous/intermittent tone(s), 100 to 110 VAC, permanent LED indicator(s), red, 30mm, panel mount, plastic housing, silver, IP00.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DR30B5-HBZC>

## Technical Specifications

<b>Brand</b>	Fuji Electric
<b>Item</b>	Audible alarm buzzer
<b>Loudness Decibel</b>	90 dB at 0.1m, 70 dB at 1m
<b>Tone Frequency</b>	2.4 kHz to 3.3 kHz
<b>Tone Type</b>	Continuous/intermittent
<b>Touch to Acknowledge</b>	No
<b>Voltage Rating</b>	100 to 110 VAC
<b>Indicator</b>	Permanent LED
<b>Light Color(s)</b>	Red
<b>Barrel Size</b>	30mm
<b>Mounting</b>	Panel
<b>Housing Material</b>	Plastic
<b>Color</b>	Silver
<b>IP Rating</b>	IP00

## Agency Approvals

<b>UL Listed File #</b>	E44592
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	LR20479
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>