

DU10105W Cut Sheet



AttaBox DuraShield series enclosure, NEMA 1/3/3S/4X/6/6P/12, 255 x 250 x 121mm (HxWxD), fiberglass reinforced polyester, Pantone 428 C glacier gray, screw cover.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DU10105W>

Technical Specifications

| | |
|---------------------------------|---------------------------------|
| Brand | AttaBox |
| Item | Enclosure |
| Series | DuraShield |
| NEMA Rating | 1/3/3S/4X/6/6P/12 |
| IP Rating | IP68 |
| Nominal Enclosure Height | 255mm |
| Nominal Enclosure Width | 250mm |
| Nominal Enclosure Depth | 121mm |
| Cover Type | Screw cover |
| Cover Depth | 25mm |
| Integral Mounting Flange | No |
| Material | Fiberglass reinforced polyester |
| Color | Pantone 428 C glacier gray |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E64358 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | LR069014 |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/DU10105W.pdf>
See store item page for other formats.