

# DVD-2AC2A-24D Cut Sheet



NITRA solenoid valve, 2-way, 2-position, N.C., brass body, 1/4in female NPT inlet(s), 1/4in female NPT outlet(s), Cv=1.55, 24 VDC operating voltage, 18mm DIN style wiring plug.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DVD-2AC2A-24D>

## Technical Specifications

Brand	NITRA
Item	Valve
Working Fluid	Air, oil, inert gas, water or emulsion
Valve Type	Solenoid process
Port Quantity	2-way
Number Of Positions	2
Valve Configuration	N.C.
Action	Single solenoid spring return
Body Material	Brass
Inlet Port	1/4in female NPT
Outlet Port	1/4in female NPT
Manual Override Type	Momentary
Flow Coefficient	1.55
Operating Voltage	24 VDC
Electrical Connection	18mm DIN style wiring plug
Form Factor	Standard
Includes	Viton seals

## Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>