

DWP-2M-0V-RL2 Cut Sheet



Lika Electronic DWP series analog linear draw wire encoder, 15-30 VDC, 0-10 VDC output, medium duty, potentiometer, 6.5ft/2m draw wire, IP64, 6.5ft/2m cable length, radial exit, pigtail.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DWP-2M-0V-RL2>

Technical Specifications

Brand	Lika Electronic
Item	Draw wire encoder
Series	DWP
Feedback Type	Analog
Encoder Type	Linear
Voltage Rating	15-30 VDC
Encoder Output Type	0-10 VDC
Duty Rating	Medium duty
Encoder Resolution	Potentiometer
Draw Wire Length	6.5ft/2m

Speed Rating	1m/sec
Flange Mount	No
Housing Material	Aluminum
IP Rating	IP64
Protection Type(s)	short circuit (between each output and common)
Cable Length	6.5ft/2m
Cable Diameter Size	6mm
Wire Size	24 AWG
Exit Orientation	Radial
Connector Type	Pigtail

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/DWP-2M-0V-RL2.pdf>
See store item page for other formats.