

E2002 Cut Sheet



Marathon XRI premium efficiency AC induction motor, inverter rated, 1hp, 3-phase, 208-230/460 VAC, 1200rpm, TEFC, NEMA 145TC frame, rolled steel, C-face/rigid base mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/E2002>

Technical Specifications

Brand	Marathon	Shaft Diameter	7/8in
Item	Motor	Shaft Material	1144 Stressproof (C-223) steel
Series	XRI	Motor Frame	NEMA 145TC
Efficiency Group	Premium efficiency	Frame Material	Rolled steel
Efficiency	82.5	Electrically Reversible	Yes
Voltage Type	AC	Insulation Class	Class F
Motor Type	Induction	IP Rating	IP43
Motor Application	Inverter rated	Constant Torque Rating	10:1
Horsepower Rating	1hp	Variable Torque Rating	10:1
Number of Phases	3	Service Factor	1.15
Voltage Rating	208-230/460 VAC	Integrated Brake	No
Synchronous Speed	1200rpm	NEMA Design	Design B
Nameplate RPM	1170rpm	Junction Box Orientation	F3
Overload Type	None	Mounting	C-face/rigid base
Enclosure Type	TEFC	Mounting Orientation	Horizontal
Shaft Type	Round with square key	Manufacturer Part Number	145TTFR6078

Agency Approvals

UL Listed File #	None
UL Recognized File #	E49747
UL Hazardous File #	None
CE	View CE declarations
CSA File #	002025
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/E2002.pdf>
See store item page for other formats.