


E22DB1B20X11C Cut Sheet



Eaton pushbutton, 22mm, momentary, incandescent illuminated, (1) N.O./ (1) N.C. contact(s), plastic base, plastic bezel, Operator: red/green, double headed, 58mm, rectangular, plastic, operator text "(I) and (O)", 120 VAC, transformer.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/E22DB1B20X11C>

Technical Specifications

Brand	Eaton
Item	Pushbutton
NEMA Rating	1/2/3/3R/4/4X/12/13
IP Rating	IP65 and IP66
Barrel Size	22mm
Action	Momentary
Bulb Type	Incandescent illuminated
Contact Type	(1) N.O./ (1) N.C.
Base Material	Plastic

Bezel Material	Plastic
Operator Color	Red/green
Operator Type	Double headed
Operator Size	58mm
Operator Shape	Rectangular
Operator Material	Plastic
Operator Legend	(I) and (O)
Voltage Rating	120 VAC
Voltage Regulation	Transformer

Agency Approvals

UL Listed File #	E131568
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	68551
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/E22DB1B20X11C.pdf>
See store item page for other formats.