

ECO1290.0015 Cut Sheet



Teknokol Eco series HMI Enclosure, 20 x 24 x 8in (HxWxD), suspension mount, aluminum, natural finish, clamshell single-door, 1/4-turn semi-flush.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/ECO1290.0015>

Technical Specifications

Brand	Teknokol
Item	HMI Enclosure
Series	Eco
Slope Top	No
3-Piece Assembly	No
Vented	No
IP Rating	IP55
Nominal Enclosure Dimensions	20 x 24 x 8in (HxWxD)
Enclosure Height	645.00in
Enclosure Width	545.00in
Enclosure Depth	215.00mm
Mounting	Suspension

Dual Access	No
Knockouts	No
Material	Aluminum
Finish	Natural
Cover Type	Clamshell single-door
Hinge Type	Butt hinges
Number of Hinges Per Door	2
Latch Type	1/4-turn semi-flush
Number Of Latches	3
Padlockable	No
Keylocking	No

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/ECO1290.0015.pdf>
See store item page for other formats.