

# ECX2071-24R Cut Sheet



AutomationDirect audible alarm buzzer, 80 dB at 10cm, 2.8 kHz tone frequency, pulse tone(s), 24 VAC/VDC, permanent LED indicator(s), red, 22mm, panel mount, plastic housing, red, IP65.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/ECX2071-24R>

## Technical Specifications

Brand	AutomationDirect
Item	Audible alarm buzzer
Loudness Decibel	80 dB at 10cm
Tone Frequency	2.8 kHz
Tone Type	Pulse
Touch to Acknowledge	No
Number of Alarms	1
Voltage Rating	24 VAC/VDC
Indicator	Permanent LED
Light Color(s)	Red
Barrel Size	22mm
Mounting	Panel
Housing Material	Plastic
Color	Red
IP Rating	IP65

## Agency Approvals

UL Listed File #	None
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/ECX2071-24R.pdf>  
See store item page for other formats.