

ECX4410 Cut Sheet



Comepi selector switch, IP65, 22mm, 2-position, maintained, key removable left position, operator only, thermoplastic base, thermoplastic bezel, Operator: black, key-operated, 30mm, round. Requires ECX4029-2 mounting flange and ECX10x0N-2 contact block.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/ECX4410>

Technical Specifications

Brand	Comepi
Item	Selector switch
Barrel Size	22mm
IP Rating	IP65
Number Of Positions	2
Action	Maintained
Key Removable Position	Key removable left position
Contact Type	Operator only
Base Material	Thermoplastic

Bezel Material	Thermoplastic
Operator Color	Black
Operator Type	Key-operated
Operator Size	30mm
Operator Shape	Round
Operator Material	Thermoplastic
Requires	ECX4029-2 mounting flange and ECX10x0N-2 contact block

Agency Approvals

UL Listed File #	E189258
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/ECX4410.pdf>
See store item page for other formats.