

EHCC1DIU-12 Cut Sheet



Edison modular fuse holder, with indicator, accepts Class CC fuses, 30A, 600V, 1-pole, 18-4 AWG copper only, integral pressure plate with separate spade connection, 35mm DIN rail mount. Package of 12.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/EHCC1DIU-12>

Technical Specifications

Brand	Edison	Number of Poles	1
Item	Fuse holder	Conductor Size	18-4 AWG copper only
Modular	Yes	Conductor Connection Type	Integral pressure plate with separate spade connection
Blown Fuse Indicator	Yes	SCCR Rating	200kA SCCR
Multi-Wire	No	Fuse Connection Type	Clip with reinforced spring
Accepts Fuse Class	Class CC	Mounting	35mm DIN rail
Amperage Rating	30A	Quantity per Pack	12
Voltage Rating	600V		

Agency Approvals

UL Listed File #	E300536
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	47235
RoHS Status	No
EU REACH	View EU REACH document
Other	None