

EKV12 Cut Sheet



Fibox DIN rail, unslotted, 35 mm width, 7 mm height, 6.3in length, plated steel. Package of 4. For use with ULTPCM201610.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/EKV12>

Technical Specifications

Brand	Fibox
Item	DIN rail
DIN Rail Type	Unslotted
Width	35 mm
Height	7 mm
Length	6.3in
Material	Plated steel
Quantity per Pack	4
For Use With	ULTPCM201610

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/EKV12.pdf>
See store item page for other formats.