

# EN4SD162010S16 Cut Sheet



Hammond Eclipse series enclosure, NEMA 3R/4/4X/12/13, 16 x 20 x 10in (HxWxD), wall mount, 316 stainless steel, #4 brush finish, single-door, 1/4-turn semi-flush 316 stainless steel latch.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/EN4SD162010S16>

## Technical Specifications

|                                     |                              |
|-------------------------------------|------------------------------|
| <b>Brand</b>                        | Hammond                      |
| <b>Item</b>                         | Enclosure                    |
| <b>Series</b>                       | Eclipse                      |
| <b>Subpanel</b>                     | Purchase subpanel separately |
| <b>Slope Top</b>                    | No                           |
| <b>NEMA Rating</b>                  | 3R/4/4X/12/13                |
| <b>IP Rating</b>                    | IP66                         |
| <b>Nominal Enclosure Dimensions</b> | 16 x 20 x 10in (HxWxD)       |
| <b>Enclosure Height</b>             | 16.00in                      |
| <b>Enclosure Width</b>              | 20.00in                      |
| <b>Enclosure Depth</b>              | 10.82in                      |
| <b>Mounting</b>                     | Wall                         |
| <b>Integral Mounting Feet</b>       | No                           |

|                                  |   |
|----------------------------------|---|
| <b>Integral Mounting Flange</b>  | No  |
| <b>Dual Access</b>               | No  |
| <b>Knockouts</b>                 | No  |
| <b>Material</b>                  | 316 stainless steel                           |
| <b>Finish</b>                    | #4 brush                                      |
| <b>Cover Type</b>                | Single-door                                   |
| <b>Hinge Type</b>                | Concealed hinges                              |
| <b>Number of Hinges Per Door</b> | 2   |
| <b>Latch Type</b>                | 1/4-turn semi-flush 316 stainless steel latch |
| <b>Number Of Latches</b>         | 1   |
| <b>Padlockable</b>               | No  |
| <b>Keylocking</b>                | No  |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | E65324                                 |
| <b>UL Recognized File #</b> | None                                   |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | <a href="#">View CE declarations</a>   |
| <b>CSA File #</b>           | LR21001                                |
| <b>RoHS Status</b>          | Yes (See CE Doc)                       |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |