

# EPDB702 Cut Sheet



Edison enclosed power distribution block, 760A, 1-pole, line side: 2 openings accept 500 MCM to 6 AWG, load side: 2 openings accept 500 MCM to 6 AWG, panel mount, UL 1953 listed.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/EPDB702>

## Technical Specifications

<b>Brand</b>	Edison
<b>Item</b>	Enclosed Power distribution block
<b>Amperage Rating</b>	760A
<b>Number of Poles</b>	1
<b>Line Side Openings</b>	2 openings accept 500 MCM to 6 AWG
<b>Load Side Openings</b>	2 openings accept 500 MCM to 6 AWG
<b>Mounting</b>	Panel
<b>SCCR Rating</b>	200kA SCCR
<b>UL Rating</b>	UL 1953 listed
<b>Additional Information</b>	Suitable for branch and feeder circuits

## Agency Approvals

<b>UL Listed File #</b>	E256146
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	700490
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	None