


F0-04RTD Cut Sheet



DirectLOGIC DL05/06 temperature input module, RTD, 4-channel, 16-bit resolution, input RTD type(s): Pt100, Pt1000, JPt100, Cu10, Cu25 and Ni120.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/F0-04RTD>

Technical Specifications

Brand	DirectLOGIC
Item	Input module
I/O Module Type	Temperature
Series	DL05/06
Input Signal Type(s)	RTD
Number Of Channels	4
Input RTD Signal Types	Pt100, Pt1000, JPt100, Cu10, Cu25 and Ni120
Input Resolution	16-bit
Programming Software	DirectSOFT programming software v4.0 or later

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	E200031
CE	View CE declarations
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/F0-04RTD.pdf>
See store item page for other formats.