


F0-08ADH-2 Cut Sheet



DirectLOGIC DL05/06 analog input module, 8-channel, voltage, 16-bit, input voltage signal range(s) of 0-5 VDC, 0-10 VDC, external 24 VDC required.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/F0-08ADH-2>

Technical Specifications

Brand	DirectLOGIC
Item	Input module
I/O Module Type	Analog
Series	DL05/06
Number Of Input Channels	8
Input Signal Type(s)	Voltage
Isolated Channels	No
Number of Non-Isolated Input Commons	1
Input Resolution	16-bit
Input Voltage Signal Range	0-5 VDC, 0-10 VDC
External Power Requirement	24 VDC
Programming Software	DirectSOFT programming software v4.0 or later

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	E200031
CE	View CE declarations
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document