

F2-08TR Cut Sheet



DirectLOGIC DL205 relay output module, 8-point, 12-24 VDC/12-240 VAC, (8) Form A (SPST) no-suppression, 2 isolated common(s), 4 point(s) per common, 10A/common. Removable terminal block included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/F2-08TR>

Technical Specifications

Brand	DirectLOGIC
Item	Output module
I/O Module Type	Relay
Series	DL205
Number of Output Points	8
Nominal Output Voltage	12-24 VDC/12-240 VAC
Relay Configuration	(8) Form A (SPST) no-suppression relays
Number of Isolated Commons	2

Jumper Selectable Isolation	No
Number of Points per Common	4
Load Current	10A/common
Fuse Type	User-supplied external fuse
Includes	Removable terminal block
Programming Software	DirectSOFT programming software v4.0 or later

Agency Approvals

UL Listed File #	E139594
UL Recognized File #	None
UL Hazardous File #	E200031
CE	View CE declarations
CSA File #	234884
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/F2-08TR.pdf>
See store item page for other formats.