


F2-CP128 Cut Sheet



DirectLOGIC DL205 communication module, ASCII, 3 ports, buffered, 128k program memory, 26 MHz maximum switching frequency, (1) RS-232 and (2) RS-232/RS-422/RS-485 port(s). For use with D2-240, D2-250(-1), D2-260 and D2-262 CPU-based PLCs.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/F2-CP128>

Technical Specifications

Brand	DirectLOGIC
Item	Communication module
Series	DL205
Number of Ports	3
Buffered Ports	Yes
Program Memory	128k
Maximum Switching Frequency	26 MHz
Communication Port and Connection Type(s)	<ul style="list-style-type: none">• (1) RS-232• (2) RS-232/RS-422/RS-485
Port Protocol(s)	ASCII BASIC
Port Speed(s)	up to 115.2k baud
For Use With	D2-240, D2-250(-1), D2-260 and D2-262 CPU-based PLCs
Programming Software	DirectSOFT programming software v4.0 or later
Additional Information	Not compatible with D2-230 or Do-more H2 series CPUs.
Dangerous Goods	<ul style="list-style-type: none">• Battery Installed: Yes• Packaging Instructions: 970• UN Number: UN3091• Hazard Type: Lithium Batteries• Battery Type: Button• Lithium Content: 0.04• Replacement Battery: BR1632• Generic Battery: BR1632

Agency Approvals

UL Listed File #	E139594
UL Recognized File #	None
UL Hazardous File #	E200031
CE	None
CSA File #	234884
RoHS Status	No
EU REACH	View EU REACH document