

# F25ASRL548 Cut Sheet



Eaton NEMA limit switch, side rotary 3in stainless steel lever with Nylatron roller, 90-degree adjustable head, (1) N.O./ (1) N.C. contact(s), snap action, 29.4mm x 60mm hole spacing, die-cast zinc, (1) 1/2in NPT cable entry.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/F25ASRL548>

## Technical Specifications

<b>Brand</b>	Eaton
<b>Item</b>	Limit switch
<b>Switch Type</b>	NEMA
<b>Actuator Type</b>	Side rotary 3in stainless steel lever with Nylatron roller
<b>Head Type</b>	90-degree adjustable
<b>Contact Type</b>	(1) N.O./ (1) N.C.
<b>Action</b>	Snap action

<b>Reset</b>	No
<b>Body Width</b>	39mm
<b>Mounting Hole Spacing</b>	29.4mm x 60mm
<b>Material</b>	Die-cast zinc
<b>IP Rating</b>	IP67
<b>Operating Temperature</b>	-12 to 94 deg C
<b>Connection</b>	(1) 1/2in NPT cable entry

## Agency Approvals

<b>UL Listed File #</b>	E170645
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/F25ASRL548.pdf>  
See store item page for other formats.