

# F4-08AD Cut Sheet



DirectLOGIC DL405 analog input module, 8-channel, current/voltage, 12-bit, input current signal range(s) of 0-20 mA, 4-20 mA, input voltage signal range(s) of 0-5 VDC, 0-10 VDC, 1-5 VDC, +/- 5 VDC, +/- 10 VDC, external 24 VDC required.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/F4-08AD>

## Technical Specifications

<b>Brand</b>	DirectLOGIC
<b>Item</b>	Input module
<b>I/O Module Type</b>	Analog
<b>Series</b>	DL405
<b>Number Of Input Channels</b>	8
<b>Input Signal Type(s)</b>	Current/voltage
<b>Analog Input Type</b>	Sinking
<b>Isolated Channels</b>	No
<b>Number of Non-Isolated Input Commons</b>	1
<b>Input Resolution</b>	12-bit
<b>Input Current Signal Range</b>	0-20 mA, 4-20 mA
<b>Input Voltage Signal Range</b>	0-5 VDC, 0-10 VDC, 1-5 VDC, +/- 5 VDC, +/- 10 VDC
<b>External Power Requirement</b>	24 VDC
<b>Programming Software</b>	DirectSOFT programming software v4.0 or later

## Agency Approvals

<b>UL Listed File #</b>	E139594
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>