

F4-08DA-1 Cut Sheet



DirectLOGIC DL405 analog output module, 8-channel, current, 12-bit, output current signal range(s) of 4-20 mA, external 24 VDC required.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/F4-08DA-1>

Technical Specifications

Brand	DirectLOGIC
Item	Output module
I/O Module Type	Analog
Series	DL405
Number Of Output Channels	8
Output Signal Type	Current
Analog Output Type	Sinking
Isolated Channels	No
Number of Non-Isolated Output Commons	1
Output Resolution	12-bit
Output Current Signal Range	4-20 mA
External Power Requirement	24 VDC
Programming Software	DirectSOFT programming software v4.0 or later

Agency Approvals

UL Listed File #	E139594
UL Hazardous File #	None
CE	None
RoHS Status	No
EU REACH	View EU REACH document