

F4-08THM Cut Sheet



DirectLOGIC DL405 temperature input module, thermocouple, 8-channel, 16-bit resolution, input thermocouple type(s): J, E, K, R, S, T, B, N, C.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/F4-08THM>

Technical Specifications

Brand	DirectLOGIC
Item	Input module
I/O Module Type	Temperature
Series	DL405
Input Signal Type(s)	Thermocouple
Number Of Input Channels	8
Input Thermocouple Signal Type	J, E, K, R, S, T, B, N, C
Input Voltage Signal Range	0-5 VDC, +/- 5 VDC, 0-156 mVDC, +/- 156 mVDC
Input Resolution	16-bit
External Power Requirement	24 VDC
Programming Software	DirectSOFT programming software v4.0 or later

Agency Approvals

UL Listed File #	E139594
UL Recognized File #	None
UL Hazardous File #	None
CE	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/F4-08THM.pdf>
See store item page for other formats.