

F4-08TRS-2 Cut Sheet



DirectLOGIC DL405 relay output module, 8-point, 12-24 VDC/12-240 VAC, (4) Form A (SPST) no-suppression, (4) Form C (SPDT) no-suppression, 8 isolated common(s), 1 point(s) per common, 5A/point,40A/module. Removable terminal block included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/F4-08TRS-2>

Technical Specifications

Brand	DirectLOGIC
Item	Output module
I/O Module Type	Relay
Series	DL405
Number of Output Points	8
Nominal Output Voltage	12-24 VDC/12-240 VAC
Relay Configuration	(4) Form A (SPST) no-suppression relays, (4) Form C (SPDT) no-suppression relays
Number of Isolated Commons	8
Jumper Selectable Isolation	No
Number of Points per Common	1
Load Current	5A/point,40A/module
Fuse Type	Replaceable fuse
Includes	Removable terminal block
Programming Software	DirectSOFT programming software v4.0 or later

Agency Approvals

UL Listed File #	E139594
UL Recognized File #	None
UL Hazardous File #	None
CE	None
RoHS Status	No
EU REACH	View EU REACH document