

F4-CP128-1 Cut Sheet



DirectLOGIC DL405 communication module, ASCII, 3 ports, buffered, 128k program memory, 26 MHz maximum switching frequency, (1) RS-232 and (2) RS-232/RS-422/RS-485 port(s). For use with all DL405 PLCs. Commander programming software CD-ROM for Windows included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/F4-CP128-1>

Technical Specifications

| | |
|--|--|
| Brand | DirectLOGIC |
| Item | Communication module |
| Series | DL405 |
| Number of Ports | 3 |
| Buffered Ports | Yes |
| Program Memory | 128k |
| Maximum Switching Frequency | 26 MHz |
| Communication Port and Connection Type(s) | <ul style="list-style-type: none">• (1) RS-232• (2) RS-232/RS-422/RS-485 |
| Port Protocol(s) | ASCII BASIC |
| Port Speed(s) | up to 115.2k baud |
| For Use With | All DL405 PLCs |
| Includes | Commander programming software CD-ROM for Windows |
| Programming Software | DirectSOFT programming software v4.0 or later |
| Dangerous Goods | <ul style="list-style-type: none">• Battery Installed: Yes• Packaging Instructions: 970• UN Number: UN3091• Hazard Type: Lithium Batteries• Battery Type: Button• Lithium Content: 0.01• Replacement Battery: BR1225• Generic Battery: BR1225 |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E139594 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |