

FA-GFCI Cut Sheet



AutomationDirect duplex straight blade receptacle, 15A, 125 VAC, 1-phase, 2-pole, 3-wire, ground-fault circuit interruption protection, nylon housing, panel or 35mm DIN rail mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FA-GFCI>

Technical Specifications

Brand	AutomationDirect
Item	Receptacle
Receptacle Type	Duplex
Wiring Device Type	Straight blade
Self-grounding	No
Amperage Rating	15A
Voltage Rating	125 VAC
Number of Phases	1
Number of Poles	2

Number of Wires	3
Wire Size	14-12 AWG solid or stranded
Copper Wire Only	Yes
Configuration	NEMA 5-15
Protection Type(s)	Ground-fault circuit interruption protection
Housing Material	Nylon
Mounting	Panel or 35mm DIN rail
Color	Gray
Additional Information	For laptop computers and test equipment

Agency Approvals

UL Listed File #	E139594
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/FA-GFCI.pdf>
See store item page for other formats.