


FA-ISOCON Cut Sheet



AutomationDirect serial converter, RS-232 (RJ12) to RS-422/485 (5-pin terminal), isolation protection, 5 VDC from PLC or 24 VDC external nominal input, encapsulated, DIN rail or panel mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FA-ISOCON>

Technical Specifications

Brand	AutomationDirect
Item	Serial converter
Connector Type	RS-232 (RJ12) to RS-422/485 (5-pin terminal)
Isolation Protection	Yes
Port Speed(s)	Up to 115.2k baud
Nominal Input Voltage	5 VDC from PLC or 24 VDC external
Enclosure Type	Encapsulated
Mounting	DIN rail or panel
Includes	(1) RS-232/RS-422/RS-485 converter, (1) DIN rail mounting assembly, (1) 25-pin D-shell male to RJ12 (6P6C) connector, (1) 9-pin D-shell female to RJ12 (6P6C) connector, (1) 1ft RJ12 (6P6C) to RJ11 (4P4C) cable, (1) 1ft RJ12 (6P6C) to RJ12 (6P6C) cable and (3) removable terminal blocks

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	E200031
CE	None
RoHS Status	No
EU REACH	View EU REACH document