

# FAIH-00-0E Cut Sheet



AutomationDirect photoelectric sensor, tubular, threaded, plastic housing, through-beam emitter, 20m sensing distance, 10-30 VDC operating voltage, 2-wire, 4-pin M12 quick-disconnect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FAIH-00-0E>

## Technical Specifications

Brand	AutomationDirect
Item	Photoelectric sensor
Shape	Tubular
Barrel Type	Threaded
Housing Size	18mm diameter x 67.7mm body
IP Rating	IP67
Housing Material	Plastic
Sensing Method	Through-beam emitter
Operating Voltage	10-30 VDC
Number of Wires	2
Sensing Distance	20m
Light Emission	Infrared
Connection	4-pin M12 quick-disconnect
Includes	Mounting hardware
Additional Information	Purchase cable separately

## Agency Approvals

UL Listed File #	E187310
UL Recognized File #	None
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>