

FB6-LP-0E Cut Sheet



AutomationDirect photoelectric sensor, tubular, threaded, diffuse, visible red, 400mm sensing distance, light-on, PNP, potentiometer, 1 kHz switching frequency, plastic housing, 4-pin M12 quick-disconnect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FB6-LP-0E>

Technical Specifications

| | |
|-------------------|-----------------------------|
| Brand | AutomationDirect |
| Item | Photoelectric sensor |
| Shape | Tubular |
| Barrel Type | Threaded |
| Housing Size | 18mm diameter x 33.9mm body |
| IP Rating | IP65 |
| Housing Material | Plastic |
| Sensing Method | Diffuse |
| Operating Voltage | 10-30 VDC |
| Number of Wires | 3 |

| | |
|------------------------|----------------------------|
| Switching Output | PNP |
| Sensing Distance | 400mm |
| Sensitivity | Potentiometer |
| Operation Mode | Light-on |
| Switching Frequency | 1 kHz |
| Light Emission (NP) | Visible red |
| Connection | 4-pin M12 quick-disconnect |
| Includes | Mounting hardware |
| Additional Information | Purchase cable separately |

Agency Approvals

| | |
|----------------------|--|
| UL Listed File # | E328811 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/FB6-LP-0E.pdf>
See store item page for other formats.