


# FC-33 Cut Sheet



Signal conditioner, isolated, current or voltage input, current or voltage output, 24 VDC operating voltage, 35mm DIN rail or panel mount, removable screw terminal plugs.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FC-33>

## Technical Specifications

<b>Item</b>	Signal conditioner
<b>Isolation</b>	Isolated
<b>Field Configurable</b>	Yes
<b>Input Current Signal Range</b>	0-20 mA, 4-20 mA
<b>Input Voltage Signal Range</b>	0-5 VDC, 0-10 VDC
<b>Output Current Signal Range</b>	0-20 mA and 4-20 mA
<b>Output Voltage Signal Range</b>	0-5 VDC and 0-10 VDC
<b>Operating Voltage</b>	24 VDC
<b>Housing Material</b>	Plastic
<b>Mounting</b>	35mm DIN rail or panel
<b>Electrical Connection</b>	Removable screw terminal plugs

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	E200031
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	None