


FC-R1 Cut Sheet



AutomationDirect temperature transmitter, isolated, RTD input, deg F or deg C, 4-20 mA output, 24 VDC operating voltage, 35mm DIN rail or panel mount, removable screw terminal plugs.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FC-R1>

Technical Specifications

| | |
|--------------------------------|--------------------------------|
| Brand | AutomationDirect |
| Item | Temperature transmitter |
| Isolation | Isolated |
| Field Configurable | Yes |
| Input RTD Signal Types | Pt100, Pt1000 and Cu10 |
| Programmable Temperature Range | Deg F or deg C |
| Output Current Signal Range | 4-20 mA |
| Operating Voltage | 24 VDC |
| Housing Material | Plastic |
| Mounting | 35mm DIN rail or panel |
| Electrical Connection | Removable screw terminal plugs |

Agency Approvals

| | |
|----------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | E200031 |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |